

# Mixed Oxides for Automotive TWC Applications

## Introduction

The field of Autocatalysis is very much legislation driven and this varies significantly dependent upon geographical location. This results in the need for advanced materials to meet the performance requirements, particularly after accelerated aging cycles.

Catalytic converters for gasoline vehicles simultaneously convert NO<sub>x</sub>, CO and Hydrocarbons in the exhaust (hence Three Way Catalysis, TWC). Luxfer MEL Technologies' Ceria Zirconia Mixed Oxides are a key component in this process as they act as an oxygen buffer to ensure optimal conditions for pollutant control.


We have developed customized formulations for gasoline TWC, Gasoline Particulate Filters (GPF), Diesel Oxidation Catalysts (DOC), Diesel Particulate Filters (DPF), passive NO<sub>x</sub> Absorbers (PNA), and selective catalytic reduction (SCR).

### Key TWC material attributes


- Aging Requirements
- Oxygen Storage Capacity
- Precious Metal Interaction

### Typical LMT mixed oxide properties

Material	Fresh		950 °C/2 h (Air)		1000 °C/4 h (Air)		1100 °C/12 h (HT)	
	SA (m <sup>2</sup> /g)	TPV (m <sup>3</sup> /g)	SA (m <sup>2</sup> /g)	TPV (m <sup>3</sup> /g)	SA (m <sup>2</sup> /g)	TPV (m <sup>3</sup> /g)	SA (m <sup>2</sup> /g)	TPV (m <sup>3</sup> /g)
30%CeO <sub>2</sub> (A)	106	0.36	65	0.32	49	0.27	19	0.12
30%CeO <sub>2</sub> (B)	105	0.44	67	0.31	50	0.26	18	0.11
40%CeO <sub>2</sub> (A)	87	0.42	66	0.35	49	0.28	19	0.16
40%CeO <sub>2</sub> (B)	99	0.41	52	0.32	42	0.29	22	0.12
45%CeO <sub>2</sub>	73	0.36	47	0.28	36	0.22	15	0.07



CO (~1000ppm) from inefficient combustion  
 HC (~100ppm) from incomplete combustion of fuel  
 NO<sub>x</sub> (~100ppm) reaction of N<sub>2</sub>/O<sub>2</sub> at high temperature




### Addition of Zirconia for increased thermal stability and enhanced ceria redox efficiency

Minor rare dopants for further enhancement of thermal stability and OSC properties (O-vacancies, etc.)




### 1000 °C/4 hr air aged



\*\*All materials contain additional rare-earth oxides (5-10%)


### Bare oxide (air aged 1000 °C/4hr)

- OSC testing by O<sub>2</sub> pulse
- Broadly follows Ce-level



### 0.1% Rh loaded CZ (hydrothermally aged 1100 °C/12 hr)

- OSC testing by H<sub>2</sub> pulse (i.e. lean-to-rich)
- More differentiation between samples



### Luxfer MEL Technologies' advantages

- Global supply is done from our manufacturing plants in Flemington, NJ, USA and Manchester, UK.
- In addition to a wide range of hydroxides and oxides, LMT also produces many zirconium based solutions often used as binders, adhesion promoters and sources of zirconium for catalysis.
- LMT is backward integrated by starting with zircon sand as the basic raw material.
- Luxfer MEL Technologies is committed to developing materials that offer a specific benefit in these individual applications, but with sufficient robustness that we can tailor them to suit the end user.

Discover more at  
[www.luxfermeltechnologies.com](http://www.luxfermeltechnologies.com)

† The information contained within is meant as a guideline only

Copyright © Luxfer MEL Technologies 2019. The information provided within this document is aimed to assist manufacturers and other interested parties in the use of Luxfer MEL Technologies products. Luxfer MEL Technologies accepts no liability in whole or in part from use and interpretation of the data herein. All information is given in good faith but without warranty. Freedom from patent rights must not be assumed. Health and Safety information is available for all Luxfer MEL Technologies products. **DS-1034-0619**